


TRANSFORMADOR DE TENSION VOLTAGE TRANSFORMER UTF-420

420 KV (IEC)
345 KV (IEEE)



DESCRIPCION

Aislado en papel aceite. Para conexión entre fase y tierra, con un solo polo aislado. La tensión primaria es conducida mediante una borna capacitiva formada por un conjunto de pantallas y capas de papel aislante. Diseño tipo cascada, con un solo núcleo magnético sobre el cual están arrolladas dos bobinas primarias, de forma que la tensión nominal se reparte entre ellas. Para controlar la variación del volumen de aceite, los transformadores están dotados de un compensador metálico. Indicador del nivel de aceite visible desde el exterior. Los transformadores disponen de una toma de muestras de aceite, para su posterior análisis cromatográfico.

DESCRIPTION

Oil-paper insulated. For connection between phase and earth, with a single insulated pole. The primary winding is led towards the head by means of a capacitive bushing formed by a set of screens and layers of insulating paper. Cascade type design, with a single magnetic core around which two primary coils are wound, so that the rated voltage is distributed between them. Stainless steel bellows for variations in oil volume. Oil level indicator visible from the exterior. Oil samples can be taken for chromatographic analysis, and it can be refilled with oil.

TRANSFO. TENSION
UTF 420
VOLTAGE TRANSFORMER
CARACTERISTICAS MECANICAS

Peso total	-----	1315 Kg/2899 Lbs	-----	Total weight
Peso de aceite	-----	300 Kg/661,4 Lbs	-----	Oil weight
Esfuerzos garantizados en los terminales primarios (Kg)*		200		*Guaranteed efforts on primary terminals (Kg)

MECHANICAL CHARACTERISTICS
CARACTERISTICAS ELECTRICAS

	CEI • IEC
Tensión nominal de aislamiento (kV)-----	420
Tensión máx. servicio (kV)-----	420
Tensiones de ensayo (kV)-----	630/1425
Línea de fuga standard (mm)*-----	10660

ELECTRICAL CHARACTERISTICS

	IEEE		
-----	345	-----	Highest voltage (kV)
-----	362	-----	Highest system voltage (kV)
-----	575/1300	-----	Test voltages (kV)
-----	10660	-----	*Standard creepage distance (mm)

PRESTACIONES ORIENTATIVAS
ORIENTATIVE SERVICES

POTENCIA TERMICA THERMAL BURDEN VA	Nº MAX. DE SECUNDARIOS MAX. NUMBER OF SECONDARIES	POTENCIA TOTAL SIMULTANEA TOTAL SIMULTANEOUS BURDEN					
		CEI/IEC			IEEE		
3500*	3	cl. 0,2	cl. 0,5	cl. 1	cl. 0,3	cl. 0,6	cl. 1,2
		300	700	1000	Z	ZZ	ZZ

ESTANQUEIDAD

El conjunto es hermético y funciona a presión constante.

- Prueba de hermeticidad: Se realiza a todas las unidades, bajo presión y una vez lleno el aparato de aceite, lo que garantiza la estanqueidad de los aparatos.
- El uso de tuercas de autoseguro o autoblocantes en todas las uniones herméticas garantiza el mantenimiento del par de apriete durante el tiempo de vida del aparato y, con ello, su hermeticidad.

FABRICACION

El aceite del transformador es desgasificado y filtrado con anterioridad a la impregnación. Control automático de los parámetros de los procesos de secado e impregnación bajo vacío del papel aceite. Tras el tratamiento, los transformadores pasan un largo periodo de reposo que mejora la homogeneización del aislamiento. Los arrollamientos se bobinan en máquinas automáticas con control del número de espiras y de capas de papel.

FERRORRESONANCIA

Los transformadores de tensión son reactancias saturables con núcleo de hierro que presentan diferentes valores de inductancia. La línea en la que están instalados presenta una capacitancia cambiante según que circuitos se conecten al sistema. Puede, bajo ciertas oscilaciones de tensión ajenas al transformador, producirse una resonancia mantenida entre su reactancia y capacitancia de la red, que lleve al transformador, a su destrucción por calentamiento (resonancia paralelo) o por sobretensión (resonancia serie). Un medio económico, aunque no siempre eficaz de disipar la resonancia es la conexión en triángulo abierto de los secundarios, ex-profeso para este propósito, del juego de tres transformadores de tensión. Este triángulo se cierra sobre una resistencia que disipa la energía de la ferrosresonancia. En servicio normal la tensión sobre la resistencia es cero y es como si no existiera.

CALIDAD

Control de entrada a todos los materiales y componentes en nuestro laboratorio físico-químico. Ensayos finales de rutina a todos los aparatos bajo normas internacionales y/o especificaciones particulares.

TRANSPORTE, MONTAJE Y MANTENIMIENTO

Embalados para transporte en posición horizontal o vertical. No precisan ninguna herramienta especial para su montaje. Son herméticos, están libres de mantenimiento regular y no requieren repuestos. Llevan incorporada una válvula de toma de muestras, vaciado y relleno de aceite, así como un indicador de posición del nivel de aceite.

Mayor distancia de fuga - Conectores primarios y de tierra -

Secundarios con tomas - Aislador de silicona - Otros accesorios __Opcional / Optional ____ Secondary tapings - Silicone insulator - other accesories

* Para necesidades mayores ----- Consultar / Please request ----- * For higher requirements

HERMETICITY

The transformer is hermetically sealed and works at a constant internal oil pressure

- Hermeticity test: All transformers are tested by overpressure, after filling them with oil. This way we can guarantee full hermeticity of the transformers.
- We can guarantee the stability of the torque during the life of the unit and therefore the hermeticity of the transformer by using of self locking nuts in all hermetic joints.

MANUFACTURE

The transformer oil is degassified and filtered before impregnation. The parameters of the processes of drying and impregnation of the oil-paper under vacuum are automatically controlled. After treatment, the transformers are left to rest for a long period, which makes for more even insulation. The coils are wound on automatic machines with control of the number of turns and the paper layers.

FERRORRESONANCE

The voltage transformers are saturable reactors with an iron core, and with different inductance values. The capacitance of the line in which they are installed varies according to the circuits connected to the system. Under certain voltage oscillations outside the transformer, a resonance may be produced between the reactance and the mains capacitance, which leads to the destruction of the transformer, by heating (parallel resonance) or by overvoltage (series resonance). An economical, though not always effective, way of dissipating the resonance, is to connect the secondaries of the set of three voltage transformers in an open delta configuration. This delta is closed on a resistor which dissipates the ferrosresonance energy. In normal service the voltage through the resistor is zero.

QUALITY

The control of all materials and components is made upon their arrival in our Physicochemical Laboratory. The transformers, once finished are subjected to the routine tests required by the international standards and/or customer's specifications, in the High Voltage Laboratory.

TRANSPORT, MOUNTING AND MAINTENANCE

Packaged for transport in horizontal or vertical position. No special tools are necessary for assembly. The units are hermetically sealed, need no regular maintenance and do not require spare parts. There is a valve incorporated for taking samples, emptying and refilling with oil, as well as an oil indicator on the head.

Higher creepage distance - Primary and earth connectors -

Secondary tapings - Silicone insulator - other accesories

* Para necesidades mayores ----- Consultar / Please request ----- * For higher requirements